

Botron B82450 Technical Data Sheet



Features:

Botron's B82450 Combo Test Station is a 36" solid welded steel test frame with aluminum composite floor plate and features a powder coated finish for long lasting durability. Comes equipped with the B8211 Combo Tester that can test both feet at the same time while also able to switch to wrist straps as well.

PROPERTIES

SPECIFICATIONS

| | |
|---------------------|------------------------|
| Frame: | Solid welded steel |
| Floor Plates: | Aluminum Composite |
| Frame size: | 36" |
| Plates size: | 1 1/4" x 19" x 15 1/2" |
| Tester: | B8211 |
| Battery: | 9 volt |
| LEDs: | (3) Low, OK and High |
| Alarm: | Internal buzzer |
| Test Range: | 800k - 100 MegOhm |
| Testing - Wrist: | 750k - 100 MegOhm |
| Testing - Footwear: | 750k - 100 MegOhm |
| Mounting: | Free standing |
| External Power: | AC/DC (not included) |

Wrist strap and footwear ranges are independently set +/- 5%

PART NUMBERS

B82450 Combo Tester w/stand
B82452 Replacement Plate
B82451 Combo Tester & Plate

Product Notes and Features

- Uses 9 Volt Battery
- Visual and Audible Alarms
- LED Light Indicators
- Low Battery Indicator



Distributed by: All-Spec
Ph: 800-537-0351, **Fx:** 800-379-9903
Email: sales@all-spec.com
Web Site: www.all-spec.com

Botron Company Inc. | 21601 N. 21st Avenue Phoenix AZ 85027 | Ph# 623-582-6700 | Fax# 623-582-6776

Disclaimer. All statements of technical information are believed to be true and are based upon tests we believe to be reliable. The proper use and application for this product must be the responsibility of the user. The statements herein shall have no force or effect.

OPERATION

Bolt plate onto stand with (4) screws.

Install 9 volt battery into rear compartment of tester.

Velcro tester onto test station stand.

Connect wire into bottom of tester through access holes in stand.

Plug other end of wire into fitting on bottom of plate.

With heel grounders on both feet, step onto plates and press touch plate.

When testing wrist straps, plug banana jack into front of tester. Switch to "wrist strap" setting and push touch plate.

Distributed by: All-Spec
Ph: 800-537-0351, **Fx:** 800-379-9903
Email: sales@all-spec.com
Web Site: www.all-spec.com

Botron Company Inc. | 21601 N. 21st Avenue Phoenix AZ 85027 | Ph# 623-582-6700 | Fax# 623-582-6776

Disclaimer. All statements of technical information are believed to be true and are based upon tests we believe to be reliable. The proper use and application for this product must be the responsibility of the user.

The statements herein shall have no force or effect.