




Super Adjustable™

Super Erecta®

ESD SHELVING

ASSEMBLY INSTRUCTIONS

- Super Adjustable ESD Shelving is assembled in the same manner as standard Super Adjustable shelving **except the black sleeves must be replaced with gray conductive sleeves** supplied separately in a bag of four (Cat. No. AESD-4).
- Open the green-tinted bags included in the shelving carton(s).
- **Discard the black plastic sleeves.**
- Open pink-tinted bags (Cat. No. AESD-4) supplied separately. These gray conductive sleeves will replace the black sleeves during the assembly process.
- Follow the assembly instructions supplied with the shelving, substituting the gray conductive sleeves for the black sleeves.
- For all mobile Super Adjustable ESD applications, conductive casters and/or a grounding cable (Cat. No. ASK16S) must be used to insure conductivity. Follow the instructions included with the grounding cable for attachment to bottom shelf.
- Additional gray conductive sleeves can be ordered under Cat. No. AESD-4 (bag of four sleeves for one shelf level).



Distributed by:
All-Spec Industries
 Wilmington, NC
 Web: www.all-spec.com

Ph: 800-537-0351
 Fx: 800-379-9903
 Email: sales@all-spec.com



InterMetro Industries Corporation
 North Washington Street, Wilkes-Barre, PA 18705
 For Product Information Call: 1-800-433-2232
 Visit Our Web Site: www.metro.com

L01-286
 Rev. A
 5/99

Information and specifications are subject to change without notice. Please confirm at time of order.



Super Adjustable 2™


NEW Replacement Parts



- Wedge**
- Solid front face
 - Charcoal gray color



- Release**
- 2 side flanges
 - Charcoal gray color



Side Flange


Original Super Adjustable Replacements parts no longer available.



- Original Wedge**
- Window
 - Flat front



- Original Release**
- Flat back surface
 - Black color




Flat surface

⚠ WARNING


- Super Adjustable 2 releases may NOT be used with Original Super Adjustable wedges.
- Super Adjustable 2 wedges may NOT be used with Original Super Adjustable releases.

Failure to follow these replacement part instructions could result in product failure and/or personal injury or property damage.

Do NOT mix old and new components



Do NOT mix old and new components



Sleeve design is unchanged.



Distributed by:
All-Spec Industries
 Wilmington, NC
 Web: www.all-spec.com

Ph: 800-537-0351
 Fx: 800-379-9903
 Email: sales@all-spec.com

IMPORTANT: For easiest replacement of the Super Adjustable corner release, place the shelf upside down on the floor.

Figure A: Removing the Super Adjustable Corner Release




Figure B: Installing a Super Adjustable Corner Release





Figure C: Attaching the wedge and sleeve to the post.



InterMetro Industries Corporation
North Washington St., Wilkes-Barre, PA USA 18705

For product information, call 1-800-433-2232 -or-
Visit www.metro.com

Distributed by:
All-Spec Industries
Wilmington, NC
Web: www.all-spec.com

Ph: 800-537-0351
Fx: 800-379-9903
Email: sales@all-spec.com

4/2006 INST-SA2RP

Information and specifications
are subject to change without
notice. Please confirm at time
of order.