



# STAYS (Self-Traction Accessory Yield System) LENSES



Luxo's new STAYS lenses are for use with Circus, WAVE+Plus, WAVE LED, KFM, KFM LED and LFM LED Magnifiers. 4- (2X), 6- (2.5X), or 10-diopter (3.5X) lenses are available. The diameter of the lens itself is 2" while the STAYS lens, including the silicon gasket frame, measures 2.5".

### Instructions for installation:

Before affixing the STAYS lens to the magnifier lens surface, clean the magnifier lens of all dirt and fingerprints. This will ensure maximum adherence of the STAYS lens to the magnifier lens. Then simply place the STAYS lens on the magnifier lens glass and gently press down.

Part No.	Description	Working distance when used with a 3D/3.5D lens	Working distance when used with a 5D lens
50404	4-Diopter STAYS Lens	6"	4"
50406	6-Diopter STAYS Lens	4"	3.8"
50410	10-Diopter STAYS Lens	2.9"	2.6"

Distributed by:

**All-Spec Industries**  
5228 US Hwy 421 N  
Wilmington, NC 28401

[www.all-spec.com](http://www.all-spec.com)  
[sales@all-spec.com](mailto:sales@all-spec.com)

PH: 800-537-0351  
FX: 800-379-9903