

ALPHA[®] OM-340

No-Clean Lead-Free, Fine Feature, Zero Halogen, Low HIP, Highly Pin-Testable

DESCRIPTION

ALPHA OM-340 is a lead-free, no-clean solder paste designed for a broad range of applications. **ALPHA OM-340** provides best in class low defect rate for Head in Pillow defects combined with excellent first pass yield on ICT/pin testing. **ALPHA OM-340** also yields excellent print capability performance across various board designs and, particularly, with ultra-fine feature repeatability and high “through-put” applications.

Outstanding reflow process window delivers superior soldering on CuOSP with excellent coalescence on a broad range of deposit sizes, excellent random solder ball resistance and mid-chip solder ball performance. **ALPHA OM-340** is formulated to deliver excellent visual joint cosmetics and best in class in circuit pin test yields. Additionally, **ALPHA OM-340's** capability of IPC Class III for voiding and ROL0 IPC classifications ensures maximum long-term product reliability.

FEATURES & BENEFITS

- Maximizes reflow yield for lead-free processing, allowing full alloy coalescence at circular dimensions as small as 200µm (8 mil) with 100µm (4 mil) thick stencils
- Excellent print consistency with high process capability index across all board designs
- Print speeds of up to 150mm/sec (6"/sec), enabling a fast print cycle time and a high throughput
- Wide reflow profile window with good solderability on various board / component finishes
- Excellent solder and flux cosmetics after reflow soldering
- Best in class low defect rate for Head in Pillow
- Best in class in circuit pin test yield
- Reduction in random solderballing levels, minimizing rework and increasing first time yield
- Meets highest IPC 7095 voiding performance classification of Class III
- Excellent reliability properties, halide-free material
- Compatible with either nitrogen or air reflow
- Zero halogen (No halogen intentionally added to the formulation)

PRODUCT INFORMATION

<u>Alloys:</u>	SAC305, SAC405, Sn96%Ag4%, SACX [®] Plus 0307, SACX Plus 0807, InnoLot, Maxrel [™] Plus
<u>Powder Size:</u>	Type 3 (25-45µm), Type 4 (20-38µm), Type 4.5 (proprietary), Type 5 (15-25µm), Type 6 (≤ 20µm)
<u>Packaging Sizes:</u>	500 gram jars, 6" & 12" cartridges, and 10cc and 30cc dispense syringes.
<u>FluxGel:</u>	OM-340 Flux Gel is available in 10cc and 30cc syringes for rework applications.
<u>Lead Free:</u>	Complies with RoHS Directive 2011/65/EU

NOTE 1: For other alloys, powder size and packaging sizes, contact your local Alpha Sales Office.

ALPHA® OM-340

No-Clean Lead-Free, Fine Feature, Zero Halogen, Low HIP, Highly Pin-Testable

APPLICATION

Formulated for both standard and fine pitch stencil printing, at print speeds of between 25mm/sec (1"/sec) and 150mm/sec (6"/sec), with stencil thickness of 100µm (4 mil) to 150µm (6 mil), particularly when used with **ALPHA Stencils**. Blade pressures should be 0.18-0.27 kg/cm of blade (1.0 -1.5 lbs/inch), depending upon the print speed. The higher the print speed employed, the higher the blade pressure that is required. The reflow process window will give high soldering yield with good cosmetics and minimized rework.

HALOGEN STATUS

HALOGEN STANDARDS			
STANDARD	REQUIREMENT	TEST METHOD	STATUS
JEITA ET-7304 <i>Definition of Halogen Free Soldering Materials</i>	< 1000 ppm Br, Cl, F in solder material solids	TM EN 14582	Pass
IEC 612249-2-21	Post Soldering Residues contain < 900 ppm each or total of < 1500 ppm Br or Cl from flame retardant source		Pass
JEDEC <i>A Guideline for Defining "Low Halogen" Electronics</i>	Post soldering residues contain < 1000 ppm Br or Cl from flame retardant source		Pass
Zero Halogen: No halogenated compounds have been intentionally added to this product			

SAFETY

While the **ALPHA OM-340** flux system is not considered toxic, its use in typical reflow will generate a small amount of reaction and decomposition vapors. These vapors should be adequately exhausted from the work area. Consult the SDS for all safety information. The most recent version of the SDS is available from AlphaAssembly.com.

STORAGE

ALPHA OM-340 should be stored in a refrigerator upon receipt at 0 to 10°C (32-50°F). **ALPHA OM-340** should be permitted to reach room temperature before unsealing its package prior to use. This will prevent moisture condensation build up in the solder paste.

ALPHA[®] OM-340

No-Clean Lead-Free, Fine Feature, Zero Halogen, Low HIP, Highly Pin-Testable

TECHNICAL DATA

CATEGORY	RESULTS				PROCEDURES/REMARKS
CHEMICAL PROPERTIES					
Activity Level	ROLO				IPC J-STD-004
Halide Content	Halide free (by titration). Passes Ag Chromate Test				IPC J-STD-004
Halogen Content	Pass , Zero Halogen - No halogen intentionally added				EN14582, by oxygen bomb combustion, Non-detectable (ND) at < 50 ppm
Copper Mirror	Pass				IPC J-STD-004
Copper Corrosion Test	Pass				IPC J-STD-004
ELECTRICAL PROPERTIES					
SIR (IPC 7 days @ 85°C/85% RH)	Pass (≥ 1 x 10 ⁸ ohm), 8.6 x 10 ⁹ ohms				IPC J-STD-004
SIR (Bellcore 96 hrs @ 35°C/85%RH)	Pass (≥ 1 x 10 ¹¹ ohm), 2.1 x 10 ¹¹ ohms				GR78-Core
Electromigration (Bellcore 96 hrs @ 65°C/85%RH 10V 500 hrs)	Pass (=final > initial/10), Initial = 3.9 x 10 ⁸ ohms Final = 1.9 x 10 ⁹ ohms				GR78-Core
PHYSICAL PROPERTIES (Using 88.0% Metal, IPC Type 3 Powder, unless otherwise noted)					
Color	Clear, Colorless Flux Residue				
Tack Force vs. Humidity (t=8 hours)	Pass , Change of <1 g/mm ² over 24 hrs at 25% & 75% Relative Humidity				IPC J-STD-005 TM-650 2.4.44
	Pass , Change of <10% when stored at 25±2°C and 50±10% relative humidity.				JIS Z3284 Annex 9
Metal Content	88% for printing with Type 3 Powder	84% to 85% for dispensing; 88.3% for printing with Type 4 Powder	78% for dispensing; 88.1% for printing with Type 5 Powder	78% for dispensing with Type 6 Powder	Malcom Spiral Viscometer; J-STD-005
Viscosity @ 10RPM	1600 Poise Target Viscosity for printing	600 up to 800 Poise Target Viscosity for dispensing; 1800 Poise Target Viscosity for printing	400 Poise Target Viscosity for dispensing; 1800 Poise Target Viscosity for printing	400 Poise Target Viscosity	
Solderball	Acceptable (SAC 305 and SAC405)				IPC J-STD-005
	Pass , Class I - 1 hour and 72 hour				DIN Standard 32 513, 4.4

ALPHA[®] OM-340

No-Clean Lead-Free, Fine Feature, Zero Halogen, Low HIP, Highly Pin-Testable

Stencil Life	> 8 hours	@ 50%RH, 25°C (74°F)
Spread	Pass	JIS-Z-3197: 1999 8.3.1.1
Slump	Pass	IPC J-STD-005 10min 150°C) TM-650 2.4.35
	No bridging 0.2 mm gap & above	JIS-Z-3284-1994 Annex 7
	No bridging 0.3 mm gap & above	JIS-Z-3284-1994 Annex 8

PROCESSING GUIDELINES


ALPHA OM-340 Processing Guidelines			
STORAGE & HANDLING	PRINTING	REFLOW (See Fig 1 & 2)	CLEANING
<ul style="list-style-type: none"> Refrigerate to guarantee stability @ 0-10°C (32-50°F) Shelf life of refrigerated paste is 6 months. Paste can be stored for 2 weeks at room temperatures up to 25°C (77°F) prior to use. When refrigerated, warm-up of paste container to room temperature for up to 4 hours. Paste must be ≥19°C (66°F) before processing. Verify paste temperature with a thermometer to ensure paste is at 19°C (66°F) or greater before setup. Printing can be performed at temperatures up to 32°C (89°F). Paste can be manually stirred before use. A rotating, centrifugal force mixing operation is not required. If a rotating/centrifugal force mixing is used, 30 - 60 seconds at 300 RPM is adequate. Do not remove worked paste from stencil and mix with unused paste in jar. This will alter rheology of unused paste. These are starting recommendations and all process settings should be reviewed independently. 	<p>STENCIL: Recommend ALPHA CUT, ALPHA NICKEL-CUT, ALPHA TETRABOND[®], or ALPHA FORM stencils @ 0.100mm - 0.150 mm (4-6 mil) thick for 0.4 - 0.5 mm (0.016" or 0.020") pitch. Stencil design is subject to many process variables. Contact your local ALPHA Stencil site for advice.</p> <p>SQUEEGEE: Metal (recommended)</p> <p>PASTE ROLL: 1.5-2.0 cm diameter and make additions when roll reaches 1-cm (0.4") diameter (min). Max roll size will depend upon blade</p> <p>PRESSURE: 0.45 to 0.7 kg/inch</p> <p>SPEED: 25 to 150mm per second (1 to 6 inches per second).</p> <p>STENCIL RELEASE SPEED: 3-10mm/sec.</p> <p>PRINT PUMP HEAD: Passes DEK ProFlow[®] compatibility test</p>	<p>ATMOSPHERE: Clean-dry air or nitrogen atmosphere.</p> <p>PROFILE (SAC Alloys): Acceptable reflow / coalescence for feature size down to 8 mil (200 µm). IPC Class III voiding obtained for both straight ramp and soak profiles.</p> <p>Compatible with most common surface finishes. (Entek HT, Entek OM, Alpha Star, ENIG, SACX HASL)</p> <p>NOTE 2: Refer to component and board supplier data for thermal properties at elevated temperatures. Lower peak temperatures require longer TAL for improved joint cosmetics. Keeping the peak temperature below 240°C will lower the amount of voiding.</p>	<p>ALPHA OM-340 residue is designed to remain on the board after reflow.</p> <p>If reflowed residue cleaning is required, the following aqueous cleaners are recommended: In-line or Batch Cleaners - ALPHA BC-2200 - Zestron Vigon A201 - Zestron Vigon A250 - Zestron Vigon US</p> <p>Manual or solvent cleaning: - ALPHA SM-110 - ALPHA SM-110E</p> <p>Misprints and stencil cleaning may be done with the following cleaners: ALPHA SM- 10E ALPHA SM-440 Zestron Vigon SC200</p>

ALPHA® OM-340

No-Clean Lead-Free, Fine Feature, Zero Halogen, Low HIP, Highly Pin-Testable

ALPHA OM-340 - General Reflow Profile Guidelines	
Parameter	Guideline
Atmosphere	Air or N2
SAC305, SAC405	217 - 221°C Melting Range
SACX Plus™ 0807	217 - 225°C Melting Range
SACX Plus™ 0307	217 - 227°C Melting Range
Maxrel Plus™	211 - 216°C Melting Range
InnoLot™	206 - 217°C Melting Range


Figure 1: Typical Soak Reflow Profile for SAC305 Alloy



ALPHA® OM-340

No-Clean Lead-Free, Fine Feature, Zero Halogen, Low HIP, Highly Pin-Testable

Figure 2: Typical Ramp Reflow Profile for SAC305 Alloy



NOTE 3: The processing guidelines recommended and typical reflow profiles presented were tested in the lab with acceptable performance. Optimization to each board application should still be carried out by users to ensure best results.

ALPHA® OM-340

No-Clean Lead-Free, Fine Feature, Zero Halogen, Low HIP, Highly Pin-Testable

CONTACT INFORMATION

To confirm this is the most recent issue, please contact Alpha Assembly Solutions

AlphaAssembly.com

<p>North America 300 Atrium Drive Somerset, NJ 08873, USA 800.367.5460</p>	<p>Europe Unit 2, Genesis Business Park Albert Drive Woking, Surrey, GU21 5RW, UK 01483.758400</p>	<p>Asia 8/F., Paul Y. Centre 51 Hung To Road Kwun Tong, Kowloon, Hong Kong 852.3190.3100</p>
-----------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------

Also read carefully warning and safety information on the Safety Data Sheet. This data sheet contains technical information required for safe and economical operation of this product. READ IT THOROUGHLY PRIOR TO PRODUCT USE. Emergency directory assistance Chemtrec 1 - 800 - 424 - 9300.

DISCLAIMER: All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. No statement or recommendation shall constitute a representation unless set forth in an agreement signed by officers of seller and manufacturer. NO WARRANTY OR MERCHANTABILITY OR WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE IS MADE. The following warranty is made in lieu of such warranties and all other warranties, express, implied, or statutory. Products are warranted to be free from defects in material and workmanship at the time sold. The sole obligation of seller and manufacturer under this warranty shall be to replace any product defective at the time sold. Under no circumstances shall manufacturer or seller be liable for any loss, damage or expense, direct or consequential, arising out of the inability to use the product. Notwithstanding the foregoing, if products are supplied in response to a customer request that specifies operating parameters beyond those stated above, or if products are used under conditions exceeding said parameters, the customer by acceptance or use thereof assumes all risk of product failure and of all direct, indirect and consequential damages that may result from use of the products under conditions, and agrees to exonerate, indemnify and hold harmless MacDermid Incorporated therefrom. No suggestion for product use nor anything contained herein shall be construed as a recommendation to use any product in infringement of any patent rights, and seller and manufacturer assume no responsibility or liability for any such infringement.

® Registered Trademark of MacDermid Performance Solutions. ™ Trademark of MacDermid Performance Solutions.
© Platform Specialty Products Corporation and its subsidiaries 2016.