
< DUPONT >

DUPONT[™] TYVEK® 400 TY210S WH

GARMENT TECHNICAL DATA SHEET



This picture is for measurement reference only.

Customer Service:

North America 1-800-931-3456

SafeSPEC[™] Home Page

Seams and closures have less barrier than fabric. Note: for protection from hazardous or infectious liquids, additional barrier tests are required to establish suitability for use. CAUTION: This information is based upon technical data that DuPont believes to be reliable. It is subject to revision as additional knowledge and experience are gained. DuPont makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics, not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under the specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures may provide less barrier than the fabric. If the fabric becomes torn, abraded, or punctured, end-user should discontinue use of garment to avoid compromising the barrier protection. SINCE CONDITIONS OF USE ARE OUTSIDE OUR CONTROL, WE MAKE NO WARRANTES, EXPRESSED OR MIPLIED, INCLUDING WITHOUT LIMITATION NO WARRANTES OF MERCHANTABLITY OR FITNESS FOR A PARTICULAR USE AND ASSUME NO LIABILITY IN CONVECTION WITH ANY OF THIS INFORMATION. This information is not intended as a license to operate under or a recommendation to infinge any patent, trademark or technical information of DuPont or others covering any material or its use. Data presented does not comprise a product specification.

Warning: Cleanroom apparel should not be used around heat, flames, sparks or in potentially flammable or explosive environments. Cleanroom fabrics should have slipering could also in the outer sole of boots, shoe covers, or other gament surfaces in conditions where slipping could occur.

Silicone Statement: In the past, DuPont has found that threads and zippers can be the most significant source of silicone oil contamination in garments. DuPont specifies that thread and zippers used in DuPont[™] Tyvek® IsoClean® and ProClean® garments be manufactured without the use of silicone oils. For end uses with concerns about contamination with silicone oils or any other contaminants, the best practice is to audit inbound materials, including garments, for those contaminants.

Latex Statement: As of January 1, 2006, DuPont production specifications exclude use of components containing natural rubber latex in the manufacture of DuPontTM Tyvek® (soClean® and ProClean® garments. Anyone who begins to exhibit allergic response during the use of DuPont products should immediately cease using these products. The incident should also be reported to DuPont at 1.800.441.3637.

Measurements are approximate values intended to assist in proper size selection. Normal variability may result in slight differences in actual garment sizes.

Copyright © 2019 DuPont de Nemours Inc. All rights reserved. The DuPont Oval Logo, DuPont^{rue}, and all products denoted with @ or ^{Tw} are trademarks or registered trademarks of DuPont or its affiliates. Printed on: December 30, 2019

PRODUCT INFORMATION							
ATTRIBUTES		DuPont™ Tyvek® 400 Frock. Collar. Open Wrists. Extends Below Hip. Front Snap Closure. Serged Seams. White.					
CATALOG NUMBER TY210SWHxx0030yy (xx=size;yy=option code) When ordering, replace xx with desired size.							
FABRIC / MATERIAL	DESIGN S	EAM CO	LOR QUANTIT	Y/BOX SIZES	OPTION CODES		
Tyvek® 400	Frock S	erged Wi	nite 30 per d	Case SM, MD, LG XL, 2X, 3X, 4X, 5X, 6X,	00 VP		
				7X			
TYPICAL	FINISHED DIN	IENSIONS					
TYPICAL SIZE	FINISHED DIN SLEEVE LENGTH		BODY LENGTH		FITS HEIGHT		
			BODY LENGTH 31	7X			
SIZE	SLEEVE LENGTH	CHEST WIDTH		7X FITS CHEST	FITS HEIGHT		
size SM	SLEEVE LENGTH 30 1/2	CHEST WIDTH 22 3/4	31	7X FITS CHEST 32 1/4 - 35 3/4	FITS HEIGHT 5'0" - 5'7"		
SIZE SM MD	SLEEVE LENGTH 30 1/2 32 1/4	CHEST WIDTH 22 3/4 24 3/4	31 34	7X FITS CHEST 32 1/4 - 35 3/4 36 1/4 - 39 3/4	FITS HEIGHT 5'0" - 5'7" 5'3" - 5'7"		
SIZE SM MD LG	SLEEVE LENGTH 30 1/2 32 1/4 33 3/4	CHEST WIDTH 22 3/4 24 3/4 25 3/4	31 34 36 1/2	7X FITS CHEST 32 1/4 - 35 3/4 36 1/4 - 39 3/4 38 1/4 - 41 3/4	FITS HEIGHT 5'0" - 5'7" 5'3" - 5'7" 5'5" - 5'9"		
SIZE SM MD LG XL	SLEEVE LENGTH 30 1/2 32 1/4 33 3/4 34 3/4	CHEST WIDTH 22 3/4 24 3/4 25 3/4 27 1/2	31 34 36 1/2 39	7X FITS CHEST 32 1/4 - 35 3/4 36 1/4 - 39 3/4 38 1/4 - 41 3/4 41 3/4 - 45 1/4	FITS HEIGHT 5'0" - 5'7" 5'3" - 5'7" 5'5" - 5'9" 5'8" - 6'2"		
SIZE SM MD LG XL 2X	SLEEVE LENGTH 30 1/2 32 1/4 33 3/4 34 3/4 35 3/4	CHEST WIDTH 22 3/4 24 3/4 25 3/4 27 1/2 28 3/4	31 34 36 1/2 39 41 3/4	7X FITS CHEST 32 1/4 - 35 3/4 36 1/4 - 39 3/4 38 1/4 - 41 3/4 41 3/4 - 45 1/4 44 1/4 - 47 3/4	FITS HEIGHT 5'0" - 5'7" 5'3" - 5'7" 5'5" - 5'9" 5'8" - 6'2" 6'0" - 6'4"		

PHYSICAL PROPERTIES	Typical values, not specifications.	
PROPERTY	TEST METHOD	RESULT
Thickness	ASTM D1777	5.9 mils
Basis Weight	ASTM D3776	1.2 oz/yd ₂
Burst Strength - Mullen	ASTM D774	50 psi
Seam Strength	ASTM D1683	> 19 lb _f
Breaking Strength - Grab (MD)	ASTM D5034	18 lb _f /in
Breaking Strength - Grab (CD)	ASTM D5034	22 lb _f /in
Hydrostatic Head	AATCC 127	45 inches H ² O
Surface Resistivity (25°C / 55& RH)	ASTM D257	< 6.3 x 10^9 ohms/square
Wearing Apparel Flammability	16 CFR 1610 🕐	Class 1

52 3/4

55 1/4

59 1/4 - 62 3/4

62 3/4 - 66 1/4

6'9" - 7'1"

7'0" - 7'4"

36 1/4

38

6X

7X

39 3/4

40 3/4